

# FTTH / Inhouse

DiaLink for Room-2-Room



# DiaLink features and benefits






- Easy handling (push-pull)
- Slim design, 5 mm Ø
- Multiple use : OTO, BEP, as DiaLink-Saver or as extension
- Can be pulled directly into ducts/tubes
- Permanently protected ferrules avoiding contamination and damage
- Exceptional optical values (IL/RL)

#### DiaLink connector installation









Easy mating thanks to the hybrid adapter in the wall outlet (OTO).



Only a few steps and the OTO is ready to be used

#### The DiaLink-Saver



- Special features of the DiaLink-Saver
  - →Increased safety
  - → Can be used as extension from the OTO to the ONT
- The DiaLink-Saver acts as a breakaway device until 20N pulling force applied to the cable, avoiding damage of the OTO or ONT.










### Cabling options from OTO directly to the ONT






# Cabling options

#### from OTO to ONT with DiaLink-Saver





# Application example






Connection from OTO to the ONT under the wooden lath.

## **Cabling Options**

#### from OTO to ONT through the extension (OE)





# Application example:





Free standing connection between OTO and ONT.

The DiaLink-Saver acts as a breakaway device avoiding damage of the devices and diminishing the risk of injuries.